


## 4 CHW Logger

### DESCRIPTION

4-channel washing solution weight logger, **4 CHW Logger** provides automatic control of rinsing solution and waste volumes. The washer shows remaining volume for each bottle as percentage and gives a warning message in case of low solution volume or full waste bottle when **4 CHW Logger** is connected.

### SPECIFICATIONS

Max. loading per scale cup	2 kg
Overall dimensions (W×D×H)	267 × 252 × 97 mm
Weight	3 kg



### CAT. NUMBER

BS-060102-AK

4CHW Logger

### ACCESSORIES



**3D-IW8**  
BS-060102-AAI  
Inteliwasher

Inteliwasher **3D-IW8** series microplate washer is designed for washing various types of standard 96-well microtitre plates, microstrips as well as microarrays on FastFRAME (rectangular well shape). It is suitable for ...

[read more](#)



**IW-8**  
BS-060106-AAI  
Intelispeed washer

Intelispeed Washer **IW-8** is designed for washing of standard flat-bottom 96 well plates and microstrips. The unit is fully programmable ensuring multi-step solution ripening, aspiration (aspiration, combination of aspiration/liquid dispensing ...

[read more](#)



**IW-8m**  
IVD certified  
Intelispeed washer IVD

Intelispeed Washer **IW-8m** (IVD version) is designed for washing of standard flat-bottom 96 well plates and microstrips. The unit is fully programmable ensuring multi-step solution ripening, aspiration (aspiration, combination of ...

[read more](#)