

UP-330, platform

DESCRIPTION

Universal platform with adjustable bars can accommodate laboratory glassware of different shapes.

SPECIFICATIONS

Working area

300 × 400 × 80 mm

Flask volume

universal



CAT. NUMBER

BS-010145-AK

Platform UP-330

ACCESSORIES



HB-330
BS-010145-BK

Additional holding bar for UP-330



PSU-20i
Without platform
Multi-functional Orbital Shaker

Shaker PSU-20i provides three motion types: orbital, reciprocal and vibrating, which can be performed separately, pairwise and sequentially in repeated cycles. Shaker is designed for applications both in small specialized ...

[read more](#)