

B2-50, block

DESCRIPTION

Ø48 mm x 2 sockets depth 58 mm

SPECIFICATIONS

Depth	58 mm
Capacity	2
Diameter	48 mm



CAT. NUMBER

BS-010418-AK

B2-50



CH 3-150
Without thermoblock
Heating and cooling thermostat

Combitherm-2 CH 3-150 is specially designed to thermostabilise materials at temperatures from -3°C to $+150^{\circ}\text{C}$ according to methods of analysis. To obtain useful functionality and decrease foot-print of instruments Combitherm-2 ...

[read more](#)